

NH fuse enclosure

# GTT 411



## GTT 411

**NH fuse enclosure**

**CUSTOMIZABLE**

Productnumber: 02641101

Dimensions: 320 x 640 x 179 mm

NH fuse enclosure - Industrial Quality-, 1 x NH 1-fuse switch disconnecter, Screw connection M10, PE/N terminal M10, assembled on mounting plate, 4 x enclosure connectors (GGV)

**with transparent cover**



## Technical Data

### electrical characteristics

Rated operating voltage AC:	690 V
Rated operating voltage DC:	440 V
Rated insulation voltage AC:	690 V
Rated insulation voltage DC:	1000 V
Protection class:	II
Type of protection:	IP65
Rated current:	250 A
UL Type Rating:	3R

### Dimensions

Width:	320 mm
Length:	640 mm
Height:	179 mm

### Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	yes

### mechanical properties

Impact strength:	IK08
Cover screw torque:	2.5 Nm
Stackable:	yes

### Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %

### Ambient conditions

Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

### Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Polyamide, glass-fibre reinforced

## Accessories

[07251401 - GFS 14-m - Flange set](#)

[07673101 - KPK NH 1 - Prism terminal](#)

[07674101 - KRK NH 1 - Frame clamp for NH1 isolator](#)

[07672101 - KSK NH 1 - Lug terminal](#)