

Terminal

KLS PE 35-SL

KLS PE 35-SL

Terminal

Productnumber: 07422301

Dimensions: 58 x 53 x 23,8 mm

PE/N terminal for installation in GTA distribution boards as additional terminals or for replacement

1 module, Green, 76 A, 2 x 25 mm² + 14 x 4 mm² for NS 35



Technical Data

electrical characteristics

| | |
|--|---------------------|
| Rated operating voltage AC: | 450 V |
| Rated current: | 76 A |
| Number of poles: | 1 |
| shockproof: | Yes |
| Connection 1: Connection type: | Screws |
| Connection 1: Clamping points per pole: | 2 |
| Connection 1: Suitable for Cu conductors: | 1 |
| Connection 1: Connectable conductor cross-section, fine-wire with ferrule (min): | 2.5 mm ² |
| Connection 1: Connectable conductor cross-section, fine-wire with ferrule (max): | 16 mm ² |
| Connection 1: Connectable conductor cross-section, single-wire (min): | 2.5 mm ² |
| Connection 1: Connectable conductor cross-section, single-wire (max): | 25 mm ² |
| Connection 1: Connectable conductor cross-section, stranded (min): | 2.5 mm ² |
| Connection 1: Connectable conductor cross-section, stranded (max): | 25 mm ² |
| Connection 2: Connection type: | Screwless |
| Connection 2: Stripping length: | 10 mm |
| Connection 2: Clamping points per pole: | 14 |
| Connection 2: Suitable for Cu conductors: | 1 |
| Connection 2: Connectable conductor cross-section, fine-wire with ferrule (min): | 0.5 mm ² |
| Connection 2: Connectable conductor cross-section, fine-wire with ferrule (max): | 4 mm ² |
| Connection 2: Connectable conductor cross-section, single-wire (min): | 0.5 mm ² |

Dimensions

| | |
|---------|---------|
| Width: | 58 mm |
| Length: | 53 mm |
| Height: | 23.8 mm |

Material characteristics

| | |
|--|--------|
| Flammability class according with UL94: | V0 |
| Glow-wire flammability according to EN 60695-2-11: | 960 °C |
| Industry quality: | no |