

E-Bike charging station

TG BCS 3 BE/FR LED



TG BCS 3 BE/FR LED

E-Bike charging station

Productnumber: 20013401

Dimensions: 202 x 152 x 110 mm

E-Bike charging station, protection class IP44, black, incl. cover screw with special head, cable entries, 1 x M25 rear housing side, 1 x M25 lower housing side, 1 x ventilation seal M20, pre-wired to terminal Wago 221 (L1/L2/L3/N/PE)

Cable insertions:

Bottom: DMS 1 x M25

Rear: DMS 1 x M25

with LED lighting

equipped with:

- 3 x Protective contact socket, French/Belgian standard (on front), 230V



Technical Data

Built-in devices

Protective contact socket, French/Belgian standard (on front), 230V :	3
---	---

electrical characteristics

Rated insulation voltage AC:	400 V
Protection class:	II
Type of protection:	IP44
Number of rows:	0

Colours

Base unit colour:	black
Cover colour:	black

Dimensions

Width:	202 mm
Length:	152 mm
Height:	110 mm
Inner length:	195 mm
Inner width:	145 mm
Inner height:	76 mm

Material characteristics

UV-resistant:	yes
Halogen free:	yes
Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	750 °C
Industry quality:	yes

mechanical properties

Type of fastening:	Wall mounting
--------------------	---------------

mechanical properties

Impact strength:	IK08
------------------	------

Ambient conditions

max. relative humidity 25°C:	95 %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-35 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C
Installation location:	protected outdoor areas

Material

Base unit material:	Polycarbonate
Cover material:	Polycarbonate
Sealing material:	Polyurethane
Cover screw material:	Stainless steel V2A

Accessories

[20003101 - BCS WP1 - Weather protection cover](#)

[20003201 - BCS WP2 - Earth spike](#)

[20003301 - Bit TX20-89 - Special Bit](#)

Cable gland



|

M25