

Twist nipple

## WNI M20/sw



### WNI M20/sw

**Twist nipple**

Productnumber: 21302001

Dimensions: 24 x 24 x 20 mm

Twist nipple, IP54, M<sub>20</sub> x 1.5 mm with open sealing membrane, polyethylene, black

**Sealing range 8 - 13,5 mm, Thread length 12 mm**



---

## Technical Data

### electrical characteristics

---

|                     |      |
|---------------------|------|
| Type of protection: | IP54 |
|---------------------|------|

---

### Colours

---

|                   |            |
|-------------------|------------|
| Accessory colour: | deep black |
|-------------------|------------|

---

### Dimensions

---

|        |       |
|--------|-------|
| Width: | 24 mm |
|--------|-------|

---

|         |       |
|---------|-------|
| Length: | 24 mm |
|---------|-------|

---

|         |       |
|---------|-------|
| Height: | 20 mm |
|---------|-------|

---

### Material characteristics

---

|               |    |
|---------------|----|
| UV-resistant: | no |
|---------------|----|

---

|               |     |
|---------------|-----|
| Halogen free: | yes |
|---------------|-----|

---

|   |    |
|---|----|
| Flammability class according with UL94: | HB |
|---|----|

---

|  |        |
|--|--------|
| Glow-wire flammability according to EN 60695-2-11: | 650 °C |
|--|--------|

---

|                   |    |
|-------------------|----|
| Industry quality: | no |
|-------------------|----|

---

### mechanical properties

---

|                         |      |
|-------------------------|------|
| for wall thickness max: | 9 mm |
|-------------------------|------|

---

|                        |      |
|------------------------|------|
| for sealing range min: | 8 mm |
|------------------------|------|

---

|                        |         |
|------------------------|---------|
| for sealing range max: | 13.5 mm |
|------------------------|---------|

---

|                         |      |
|-------------------------|------|
| for wall thickness min: | 1 mm |
|-------------------------|------|

---

### Ambient conditions

---

|                        |         |
|------------------------|---------|
| Installation location: | Indoors |
|------------------------|---------|

---