

Main cable junction terminal

HA 25-42

HA 25-42


Main cable junction terminal

Productnumber: 69142201

Dimensions: 130 x 50 x 58 mm

Main cable junction terminal with cross-sectional area 1x25 mm² per pole and 2 outlets 16 mm² per pole

4-pole - 25/16 mm²



Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Number of poles:	4
Connection 1: Connection type:	Screws
Connection 1: Clamping points per pole:	3
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (min):	2.5 mm ²
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (max):	16 mm ²
Connection 1: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	25 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	25 mm ²
Connection 2: Connection type:	Screws
Connection 2: Suitable for Cu conductors:	1
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (max):	10 mm ²
Connection 2: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, single-wire (max):	16 mm ²
Connection 2: Connectable conductor cross-section, stranded (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, stranded (max):	16 mm ²

Dimensions

Width:	130 mm
Length:	50 mm
Height:	58 mm

Material characteristics

Flammability class according with UL94:	V0
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

mechanical properties

Connection 1: Tightening moment:	2.5 Nm
Connection 2: Tightening torque:	2.5 Nm

Material

Insulating body material:	Thermoplastic
---------------------------	---------------