


Main cable junction terminal

## HA 25-46



### HA 25-46

**Main cable junction terminal**

Productnumber: 69142601

Main cable junction terminal with cross-sectional area 1x25 mm<sup>2</sup> per pole and 2 outlets 16 mm<sup>2</sup> per pole, 1 x 25 mm<sup>2</sup> per pole and 2 outlets 16 mm<sup>2</sup> per pole, 4 outputs 16A mm<sup>2</sup> on fourth pole

**4-pole - 25/16<sup>2</sup>, 6x PE/N**

## Technical Data

### electrical characteristics

Rated operating voltage AC:	400 V
Number of poles:	4
Connection 1: Connection type:	Screws
Connection 1: Suitable for Cu conductors:	1
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (min):	2.5 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (max):	16 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (min):	1.5 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, single-wire (max):	25 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (min):	1.5 mm <sup>2</sup>
Connection 1: Connectable conductor cross-section, stranded (max):	25 mm <sup>2</sup>
Connection 2: Connection type:	Screws
Connection 2: Suitable for Cu conductors:	1
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (min):	1.5 mm <sup>2</sup>
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (max):	10 mm <sup>2</sup>
Connection 2: Connectable conductor cross-section, single-wire (min):	1.5 mm <sup>2</sup>
Connection 2: Connectable conductor cross-section, single-wire (max):	16 mm <sup>2</sup>
Connection 2: Connectable conductor cross-section, stranded (min):	1.5 mm <sup>2</sup>
Connection 2: Connectable conductor cross-section, stranded (max):	16 mm <sup>2</sup>

### Material characteristics

Flammability class according with UL94:	V0
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

## mechanical properties

Connection 1: Tightening moment:	2.5 Nm
Connection 2: Tightening torque:	2.5 Nm

## Material

Insulating body material:	Thermoplastic
---------------------------	---------------