

Socket enclosure

STG 008



STG 008

Socket enclosure

CUSTOMIZABLE

Productnumber: 73220801

Dimensions: 250 x 200 x 122 mm

Socket enclosure, protection class IP44, with integrated, pre-wired sockets, high mechanical resilience, non-sensitive to temperature, combinable, halogen-free

Cable insertions:

Top: Pre-embossing 8 x M20, 2 x M20/25, 1 x M32/40

Bottom: Pre-embossing 8 x M20, 2 x M20/25, 1 x M32/40

Left: Pre-embossing 2 x M20

Right: Pre-embossing 2 x M20

Rear: Pre-embossing 2 x M20/25

equipped with:

- 8 x SCHUKO® plug socket (on front), 230V

Accessories supplied:

Attachment bushes: 2x M25, 2x M32, sealing plugs



Technical Data

Built-in devices

SCHUKO® plug socket (on front), 230V:	8
---------------------------------------	---

electrical characteristics

Rated insulation voltage AC:	400 V
------------------------------	-------

Protection class:	II
-------------------	----

Type of protection:	IP44
---------------------	------

Number of rows:	0
-----------------	---

Colours

Base unit colour:	grey
-------------------	------

Cover colour:	grey
---------------	------

Dimensions

Width:	250 mm
--------	--------

Length:	200 mm
---------	--------

Height:	122 mm
---------	--------

Material characteristics

UV-resistant:	yes
---------------	-----

Halogen free:	yes
---------------	-----

Flammability class according with UL94:	V2
---	----

Glow-wire flammability according to EN 60695-2-11:	850 °C
--	--------

Industry quality:	yes
-------------------	-----

mechanical properties

Type of fastening:	Wall mounting
--------------------	---------------

Impact strength:	IK08
------------------	------

Ambient conditions

max. relative humidity 25°C:	95 %
------------------------------	------

Ambient conditions

max. relative humidity 40°C:	50 %
------------------------------	------

Min. ambient temperature:	-25 °C
---------------------------	--------

Max. ambient temperature:	40 °C
---------------------------	-------

24h ambient temperature:	35 °C
--------------------------	-------

Installation location:	protected outdoor areas
------------------------	-------------------------

Material

Base unit material:	Polycarbonate, glass-fibre reinforced
---------------------	---------------------------------------

Cover material:	Polycarbonate, glass-fibre reinforced
-----------------	---------------------------------------

Sealing material:	Polyurethane
-------------------	--------------

Cover screw material:	Polyamide, glass-fibre reinforced
-----------------------	-----------------------------------

Cable gland

