

Terminal rails

AK 14 PEN-SL



AK 14 PEN-SL

Terminal rails

Productnumber: 79031701

Dimensions: 286 x 60 x 50 mm

Screwless PE/N clamping rail, for installation in AK small distributors from AK 14 and AKL/AKi empty housings as additional terminals or for replacement requirements

Single-stage PE/N terminal rail with each, 3 screwable clamping points, 2.5 mm² - 16 mm² and 14 screwless clamping points, 1.5 - 4 mm²

Technical Data

electrical characteristics

Rated operating voltage AC:	400 V
Rated current:	76 A
Number of poles:	2
shockproof:	No
Connection 1: Connection type:	Screws
Connection 1: Strip length:	12 mm
Connection 1: Clamping points per pole:	3
Connection 1: Suitable for Cu conductors:	1
Connection 1: Suitable for Al conductors:	0
Connection 1: Connectable conductor cross-section, fine-wire without ferrule (min):	16 mm ²
Connection 1: Connectable conductor cross-section, fine-wire without ferrule (max):	1.5 mm ²
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, fine-wire with ferrule (max):	10 mm ²
Connection 1: Connectable conductor cross-section, single-wire (min):	6 mm ²
Connection 1: Connectable conductor cross-section, single-wire (max):	16 mm ²
Connection 1: Connectable conductor cross-section, stranded (min):	1.5 mm ²
Connection 1: Connectable conductor cross-section, stranded (max):	16 mm ²
Connection 2: Connection type:	Screwless
Connection 2: Stripping length:	12 mm
Connection 2: Clamping points per pole:	14
Connection 2: Suitable for Cu conductors:	1
Connection 2: Suitable for Al conductors:	0
Connection 2: Connectable conductor cross-section, fine-wire without ferrule (min):	1.5 mm ²

electrical characteristics

Connection 2: Connectable conductor cross-section, fine-wire without ferrule (max):	4 mm ²
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, fine-wire with ferrule (max):	4 mm ²
Connection 2: Connectable conductor cross-section, single-wire (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, single-wire (max):	4 mm ²
Connection 2: Connectable conductor cross-section, stranded (min):	1.5 mm ²
Connection 2: Connectable conductor cross-section, stranded (max):	4 mm ²

Dimensions

Width:	286 mm
Length:	60 mm
Height:	50 mm

Material characteristics

Flammability class according with UL94:	V2
Glow-wire flammability according to EN 60695-2-11:	960 °C
Industry quality:	no

mechanical properties

Connection 1: Tightening moment:	1.6 Nm
----------------------------------	--------

Sales Information

EAN:	4013902912469
Packing Unit Code:	C62
ETIM Class:	EC001284
Custom tariff number:	85369010

Material

Insulating body material:

Thermoplastic
