

Enclosure

## IBTronic XL Drillbox E

### IBTronic XL Drillbox E

#### Enclosure

Productnumber: 97680102

Dimensions: 255 x 280 x 92 mm

Enclosure, for prefabricated construction, for installing LV/HV/LED luminaires, suitable for subsequent installation in prefabricated ceilings 45-70 mm with  $\varnothing$  82 mm core drilling, for the installation of VDE-approved lights per DIN EN 60598 (VDE 0711), as well as with F identification or MM identification, max. installation height LV lights: 105 mm, HV lights: 110 mm, lamp output max. 50W Alu, with additional connection space, (e.g. for installing an electronic safety transformer up to max. 150 VA), rated insulation voltage: 400V AC, Halogen free

**Outlet aperture:  $\varnothing$  76 mm, ORD (Outer Ring Diameter of lights), min.  $\varnothing$  85 mm, 8 combi-conduit entry points 4 x 16 mm, 4 x 19 mm integrated conduit stopper and strain relief for conduits 16 mm, 19 mm, dowel installation at floor slab, integrated conduit adapter, sealing range M16 - M19**



## Technical Data

### electrical characteristics

Rated insulation voltage AC:	400 V
Suitable for:	Concrete construction

### Colours

Cover colour:	other
---------------	-------

### Dimensions

Width:	255 mm
Length:	280 mm
Height:	92 mm

### Material characteristics

Halogen free:	yes
Flammability class according with UL94:	HB
Glow-wire flammability according to EN 60695-2-11:	650 °C
Industry quality:	no

### mechanical properties

Type of fastening:	dowel installation at floor slab
--------------------	----------------------------------

### Ambient conditions

max. relative humidity 25°C:	- %
max. relative humidity 40°C:	50 %
Min. ambient temperature:	-25 °C
Max. ambient temperature:	40 °C
24h ambient temperature:	35 °C

### Material

Base unit material:	Polypropylene
Cover material:	Polypropylene

## Accessories

[97980301 - LMK 76 - Luminaire assembly kit](#)